

Laboratory Seed Pre-Cleaner
VIBRATORY Sieve SEPARATOR

www.mmctech.us - info@mmctech.us

Product Code C.SAS-0013/ 50x80
C.SAS-0013/ 25x40



Mmctech Inc: Advanced Laboratory Seed Cleaning and Grading Machines - Features and Specification

FUNCTION ADJUSTABLES

- ☐ Compact and easy to move
- ☐ Used in seed plants for sampling large lots
- ☐ Popular with vegetable and flower growers and in seed stores for specialized cleaning, grading, and sizing
- ☐ Many laboratory uses
- ☐ Scalper and sifter screens are standard with over 150 sizes to choose from
- ☐ Shoe uses two 10" x 15" screens, one for the top and the other for the lower separation area
- ☐ Vibration Speed
- ☐ Vacuum Channel Height
- ☐ Interchangeable Screens
- ☐ Deck Slope
- ☐ Hooper Feeder Gate
- ☐ Fan Speed

Technical Chart	Screens		Drives				Air intake	Hooper Capacity	
MODEL	No	WxL (mm)	Cleaner kW	Aspirator kW		m³/h	m³/h	i.e. Wheat kg	
			220 volt / 50 Hz 1PH						
C.SAS-0013/25X40	2	250x400	0,75	1400 rpm	0.37	1400 rpm	250	0,0063	5
C.SAS-0013/50X80	2	500x800	0,75	1400 rpm	0.37	1400 rpm	250	0,01395	10


Over All Dimensions (mm)													
MODEL	Cleaner LxWxH	Hooper LxWxH	Aspirator LxWxH	Cyclone Diameter xH	Seed Boxes			Table Top Surface Area	Shipment V(m³) in Total	Weight in Total			
					Out Put LxWxH	Scalping+ Screening LxWxH							
C.SAS-0013/25X40	500 350 460	280 250 660	400 400 828	350 828	250 104 150	100 104 180		1m²	0,5	71			
Weight: (kg)	35	5	15	8	4	(2+2) 4							
C.SAS-0013/50X80	900 600 460	310 500 660	400 400 828	350 828	500 104 180	100 104 180		0.56m²	1	90			
Weight: (kg)	50	8	13	8	7	(2+2) 4							



Mmctech Inc: Pioneering Laboratory Seed Cleaning and Grading Technology

www.mmctech.us - info@mmctech.us

Laboratory Seed Pre-Cleaner Complete System



Optional Helper Equipment


- Hooper
- Aspirator
- Mini Cyclone
- Digital Scale
- Steel Table

Supplied With

- Sample Seed Cleaning Log Book
- Tool Box
- User Manual



MINI CYCLONE




ASPIRATOR



HOOPER

Complete System Dimensions



Operation

Typical Commodity Flow

- (1) The commodity is fed to the hopper and is spread evenly across the full width of the top screen.
- (2) The product then moves across the top screen, which has openings larger than the product itself. The large foreign material is "scalped" off while the good product falls through the screen.
- (3) The bottom screen can either sift or scalp. To set up for sifting, the bottom screen openings must be smaller than the commodity being cleaned. Trash, weed seeds and splits drop through the bottom screen while the good product passes over it. When scalping, the screen openings must be larger than the product itself. The large foreign material is "scalped" off while the good product falls through the screen.
- (4) Next, the product is routed through a column of air from the top air suction fan. This suction of air effectively removes any lightweight trash and dust that may have remained after screening.
- (5) Lightweight trash is collect by a cyclone in a bag. Exhausts air leaves the cyclone through a filter.
- (6) Good, clean product is discharged at the bottom of the air chamber into a clean seed box.



All Akyürek products are the subject of continuous development and, as a result, their specification may change and differ in detail from that outlined in this leaflet.

Mmctech Inc: Pioneering Small Scale Seed Cleaning and Grading Technology

www.mmctech.us - info@mmctech.us